# Shin-Etsu Silicone / 信越シリコー:

# Insulating Glass Sealant SEALANT-FC-312

SEALANT-FC-312 is a two-part silicone sealant for a secondary sealant in both structural and non-structural insulating glass units. It is a fast-cure neutral curing silicone sealant with unprimed adhesion to a wide range of coated and annealed glass.

The sealant cures to become a high-modulus silicone rubber suitable for insulating glass application.

This sealant contributes to the superior productivity and high reliability\*.

This sealant meets the requirement of EN 1279 part 4.

\* For IG units, it is the responsibility of the glass manufacturer to determine the joint configuration for the units.

# 1 Features

- Two-part, neutral-cure RTV\* silicone sealant
- Can be used with an airless mixing system, when mixed the material has very high workability even if low temperature environments
- Standard mixing ratio: adjusted to 10 [BASE]: 1 [CAT] by volume
- Fast cure with excellent adhesion to common glass type
- Superior resistance to extremes in weather, temperature change, moisture, ozone, and ultraviolet rays
- \* RTV stands for "room temperature vulcanizing "which means that this material can be cured at room temperature

# 2 Applications

As a secondary sealant for insulating glass unit manufacture in factory

### **3** Specifications

- UL 2818 2013 Gold Standard for Chemical Emissions for Building Materials
- ASTM C1184\*1
- ASTM C920\*2
- KS F 4910\*3 G-20HM

\*I Standard Specification for Structural Silicone Sealants
\*2 Standard Specification for Elastomeric Joint Sealants
\*3 Sealants for sealing and glazing in buildings

# 5 General properties

Parameter Product name		SEALANT-FC-312	
Before mixing		BASE	CAT
Consistency		Paste	Paste
Color		White	Black
Mixing ratio by volume (weight)		100 (100)	10 (7.8)
After mixing			
Snap time at 23°C min		30 to 60	
After cured - After 7 days at 23°C/50%RH	Reference Test		
Consistency		Elastic	
Color		Black	
Density at 23°C	g/cm <sup>3</sup>	1.4	
Hardness Shore A	ASTM D2240	43	
After cured - After 21 days at 23°C/50%RH	Reference Test		
10% Tensile stress MPa	ASTM C1135	0.2	
Maximum tensile stress MPa		1	.2



(Not specified values)



Container image



[BASE] SEALANT-FC-312: 260 kg drum [CAT] CAT-FC-312: 20 kg pail



#### 6 General instruction for use

- 1) Adhesion and compatibility must be tested before the commencement of any sealant application.
- 2) Before applying the sealants, ensure that all the areas to be sealed are clean and dry.
- SEALANT-FC-312 should be mixed and dispensed with airless, metered pumping equipment. Hand mixing of the base and catalyst is not approved.
- 4) The applicator must conduct A. Butterfly Test to ensure proper mixing B. Snap Time Test to ensure that the mixed material will cure C. Adhesion Test to ensure proper adhesion to the substrate surface. For the test detail, please refer to the latest Functional Sealant Technical Manual.
- 5) The sealant should be tooled immediately after the application.
- 6) All quality control test results must be logged and archived.
- 7) The Shin-Etsu Sales Department is available or specific advise.

#### 7 Limitations

- 1) SEALANT-FC-312 remains suitable for insulated glazing applications related to structural glazing but is not approved as a replacement for SEALANT-FC-295SG.
- 2) SEALANT-FC-312 must not be used in food, medical or pharmaceutical applications.
- 3) The contents of this catalog are believed to be correct, but project conditions regarding actual application and use of Shin-Etsu sealant are beyond Shin-Etsu's control. Therefore it is the users responsibility to confirm the product meets the requirements of the application.
- 4) Shin-Etsu warrants only the sealant will confirm to Shin-Etsu's product specifications at the time of shipment, and makes no further warranties in respect of the sealant. Warranty remedy for such failure is limited to refund of purchase price or replacement of product. If applicators need extended warranty for performance of sealants, please contact the Shin-Etsu Sales Department in advance of the project inception.

# 8 Storage conditions

Temperature [BASE]: at or below 30°C, [CAT]: at or below 27°C \* Seal container tightly and store in a cool, dark place (out of direct sunlight) with good ventilation. Keep away from heat and flame.

### 9 Shelf life

[BASE]: 18 months after production date, [CAT]: 12 months after production date

Under the above storage conditions in the original unopened container

#### **10** Safety and hygiene

- Uncured SEALANT-FC-312 may cause skin irritation. When handling the products, take care to avoid contact with the skin and mucous membranes by wearing protective glasses and protective gloves. In case of skin contact, immediately wipe off with dry cloth and then flush thoroughly with running water. When using, be careful not to rub eyes with hands. In case of accidental eye contact, flush immediately with plenty of clean water for at least 15 minutes and then seek medical attention. Contact lens wearers must take special care. If the products get into the eye, the contact lens may become stuck to the eye.
- 2) Be sure to provide adequate ventilation when using the product. During curing, a small amount of Methanol gas is gradually generated. If you become uncomfortable with inhaling vapors, move to an area with fresh air immediately.
- 3) Keep out of reach of children.
- 4) Please read the Safety Data Sheets (SDS) before use. SDS can be obtained from our Sales Department.

# Shir Etsu

Silicone Division Sales and Marketing Department WPhone : +81-(0)3-6812-2411 Fax : +81-(0)3-6812-2415

Shin-Etsu do Brasil Representação de Produtos Químicos Ltda. Phone : +55-11-3939-0690 Fax : +55-11-3052-3904

Shin-Etsu Singapore Pte. Ltd.

Phone : +65-6743-7277 Fax : +65-6743-7477

Shin-Etsu Silicones (Thailand) Ltd. Phone : +66-(0)2-632-2941 Fax : +66-(0)2-632-2945

Shin-Etsu Silicone Korea Co., Ltd.

Phone : +82-(0)2-590-2500 Fax : +82-(0)2-590-2501

Shin-Etsu Silicones Vietnam Co., Ltd. Phone : +84-(0)28-35355270

Shin-Etsu Silicone International Trading (Shanghai) Co., Ltd. Phone : +86-(0)21-6443-5550 Fax : +86-(0)21-6443-5868

Shin-Etsu Silicones India Pvt. Ltd.

Phone : +91-11-43623081 Fax : +91-11-43623084

"Shin-Etsu Silicone" is a registered trademark of Shin-Etsu Chemical Co., Ltd. This is an edited version of the product data released on Apr. 2025.

#### Shin-Etsu Chemical Co., Ltd.

•The data and information presented in this catalog may not be relied upon to represent standard values. Shin-Etsu reserves the right to change such data and information, in whole or in part, in this catalog, including product performance standards and specifications without notice. • Users are solely responsible for making preliminary tests to determine the suitability of products for their intended use. Statements concerning possible or suggested uses made herein may not be relied upon, or be construed, as a guaranty of no patent infringement. • For detailed information regarding safety, please refer to the Safety Data Sheet (SDS). •The silicone products described herein have been designed, manufactured and developed solely for general industrial use only; such silicone products are not designed for, intended for use as, or suitable for, medical, surgical or other particular purposes. Users have the sole responsibility and obligation to determine the suitability of the silicone products described herein for any application, to make preliminary tests, and to confirm the safety of such products for their use. • Users must never use the silicone products described herein for the purpose of implantation into the human body and/or injection into humans. • Users are solely responsible for exporting or importing the silicone products described herein, and complying with all applicable laws, regulations, and rules relating to the use of such products. Shin-Etsu recommends checking each pertinent country's laws, regulations, and rules in advance, when exporting or importing, and before using the products. • Please contact Shin-Etsu before reproducing any part of this catalog. Copyright belongs to Shin-Etsu Chemical Co., Ltd

#### https://www.shinetsusilicone-global.com/